

**COMPATIBILE
CON TUTTI I TRASMETTITORI
A CODICE FISSO COMPRESI
NELLE FREQUENZE 433 - 868 MHz**



PROCEDURA PER SFRUTTARE LA TECNOLOGIA S.A.M. (Smart Auto Memorization)

- Dopo avere duplicato il codice del trasmettitore originale, posizionarsi in prossimità dell'automazione.
- Mantenere premuto il tasto programmato per 10 secondi circa, quando il LED inizia a lampeggiare rilasciare il tasto.
- Attendere lo spegnimento del LED a conferma di procedura ultimata.

ATTENZIONE

Alcune riceventi possono avere la radio disabilitata, in questi casi è necessario inserire i nuovi trasmettitori manualmente seguendo la procedura descritta nel relativo manuale d'istruzioni.

**COMPATIBLE
WITH ALL REMOTE CONTROLS
WITH FIXED CODE
FROM 433.92 MHz TO 868 MHz**



PROCEDURE TO EXPLOIT THE S.A.M. TECHNOLOGY (Smart Auto Memorization)

- After duplicating the original remote control code, position yourself near the automation.
- Keep the programmed key pressed for about 10/15 seconds, when the LED starts flashing release the key.
- Wait for the LED to switch off to confirm the procedure is completed.

WARNING

Some receivers or control unit may have the radio disabled, in these cases it is necessary to memorize the new remote control manually following the procedure described in the instruction manual of the original manufacturer.

COMPATIBILITÀ **FACILE** MULTIFREQUENZA

FACILE MULTIFREQUENCY COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



AGIRE SULLA RICEVENTE
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELLO / MODEL | TIPOLOGIA / MODE |
|---|---|------------------|
| ACM | TX2, TX2 COLOR, TX4 | |
| ADYX | TE4433H BLUE, 433-HG BRAVO | |
| AERF | COMPACT, HY-DOM, MERCURI B, MERCURI C, SABUTON, MARS, SATURN, ST3/N, TERRA, TMP-1, TMP-2, UNITECH | |
| AERF | MEDVA | |
| ALLMATIC | BROWN, BROWN RED, BRO.OVER, PASS, MINIPASS, TECH3 | |
| ALUTEC | AT-4N-868 | |
| APERIO | GO, GO PRO, GO MINI | |
| APERTO (Sommer) | 4020-TX03-434, TX02-434-2, TX02-868-2 | |
| APRIMATIC | TR, TM4, TXM | |
| ATA | PTX4 BLU, PTX4 PINK | |
| AVIDSEN | 104251, 104250, 104250 OLD, 104250 RED, 104257, 104350, 654250 | |
| BALLAN | FM400, FM400E | |
| BeB PROGET | BUGGY-F, EMY-F2, EMY-F4, EMY-N2, EMY-N4, ETY-T2SF, ETY-T4SF, ETY-N2, ETY-N4 | |
| ATTENZIONE POSSIBILI PERSONALIZZAZIONI NON DUPLICABILI PAY ATTENTION POSSIBLE CUSTOMIZATIONS THAT CANNOT BE DUPLICATED | | |
| BENINCA | TO. GO. WV, TWV, ROLLKEY, APPLE, LOT WCV, CUPIDO, TO.GO. QV | |
| BENINCA | IO | |
| BFT | MITTO, MITTO M, MITTO RCB, MITTO A, TRC, GHIBLI, MURALE, KLEIO | |
| CARDIN | TRQ S449, TRQ S449 GREEN (PRECODE), TXQ S449, TXQ S449 GREEN, TRQ S486, TXQ S486, S437 TX, XRADO | |
| CASALI | GENIUS/CASALI A252RC | |

COMPATIBILITÀ **FACILE** MULTIFREQUENZA

FACILE MULTIFREQUENCY COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



AGIRE SULLA RICEVENTE
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELLO / MODEL | TIPOLOGIA / MODE |
|--|--|------------------|
| CHAMBERLAIN LIFT MASTER MOTOR LIFT | 953ESTD, 371 LM, 971 LM, 84330E, 94334CE, 94333E/94334E/94335E, 9747E, 1A5639-7, 1A5477, 1A6487, 132B2372, 94330EML/9333EML/94335EML, 84330EML/84333EML/84335EML, 8747EML | |
| CLEMSA | MUTANCODE, T, T-8, E-CODE N | |
| CLEMSA | MASTERCODE MV ATTENZIONE CODICE FISSO WARNING FIXED CODE | |
| DASPI | ZERO RC | |
| DEA SYSTEM | PUNTO 278, GOLDR, GENIE R 273, GENIE R-GT2N, MIO TR, GT2M, TRN | |
| DETUMANDO | STANDARD | |
| DITEC | BIXLP, GOL4, BIXLG | |
| DOORHAN | TRANSMITTER 4 | |
| DOORMATIC | MILENY, MILENY-EVO | |
| ECOSTAR | RSC, RSE, RSZ | |
| EMFA | TE2-433, TE3-433, TE2-868, TE3-868 | |
| ERREKA | IRIS, ROLLER 2, ROLLER 433, ROLLER 868, SOL433, SOL868, VEGA 433, VEGA 868 | |
| FAAC | TML 433SLH, DL 868 SLH, XT 868 SLH, XT 433 SLH, T 868 SLH, T 433 SLH, XT 868 SLH BLACK, XT 433 SLH BLACK | |
| FAAC | XT 433 RC, TE433HG, XT4 433 RCBE | |
| FADINI | JUBI-SMALL, JUBI 433 | |
| GARDENGATE | | |
| GENIE | GITR-3, GIT, GICT390, GIFT390-1, G3T-BX, G1T-BX, GM3T, GICTD, GIFTD | |

COMPATIBILITÀ **FACILE** MULTIFREQUENZA

FACILE MULTIFREQUENCY COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



AGIRE SULLA RICEVENTE
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELLO / MODEL | TIPOLOGIA / MODE |
|----------------|---|------------------|
| GENIUS | AMIGOLD, AMIGO, KILO, JCL | |
| GENIUS | BRAVO, ECHO | |
| GIBIDI | AU1600, AU1600 WOOD, AU1680, AU1680 WOOD, DOMINO | |
| JCM | NEO, TWIN, KCM, DMIL | |
| JCM | GO, GO PORTIS, GO NORTON, FORSA, EMFA ROPER, TEC | |
| KBLUE | ETH-TEL01 | |
| KEY | 900TXB-42R, TXB 44R, SUB 44R | |
| KING GATES | CLIPPER, STYLO | |
| KLING | KUA, KUA E, KUA S | |
| LABEL | SPYCO | |
| LIFE | FIDO | |
| LINEAR | MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B | |
| MERLIN 2.0 | E945M, E943M, E940M | |
| MERLIN/PROLIFT | C945, C940, C943, M842, M844 | |
| MHOUSE | TX3, TX4, GTX4 | |
| MOOVO | MT4G | |
| NICE | SMILO, FLOR-S, VERY-VR, FLOR-S ERA | |
| NICE | ONE (ON), ON ERA, INTI, ERGO, PLANO, ONE (ON FM) | |
| NORTON | NEO, TXCD | |
| NORTON | GO NORTON, GO MINI NORTON | |

COMPATIBILITÀ **FACILE** MULTIFREQUENZA

FACILE MULTIFREQUENCY COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



AGIRE SULLA RICEVENTE
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELLO / MODEL | TIPOLOGIA / MODE |
|---|---|------------------|
| NOVOFERM | MCHS, MICRO-NOVOTRON 502, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 51, MINI-NOVOTRON 30, MINI-NOVOTRON 50, MNHS | |
| NORMSTAHL | RCV433-2 | |
| O&O | TX, T.COM R4-2, T.COM R8-2, TWIN, TX (NEO), ALFA, TORRES | |
| PECCININ | TX MENBRANA | |
| PRASTEL | MTE, MPSTLE, MPSTP2E, TCE, BFOR, TRQ-P, SLIM-E | |
| PUJOL | TWIN, VARIO, VARIO MARS, VARIO OCEAN, NEO | |
| ATTENZIONE POSSIBILI PERSONALIZZAZIONI NON DUPLICABILI PAY ATTENTION POSSIBLE CUSTOMIZATIONS THAT CANNOT BE DUPLICATED | | |
| RIB | LITHIO | |
| ROPER | NEO | |
| ROPER | GO ROPER, GO MINI ROPER | |
| SABUTOM | BROOVER, BROSTAR | |
| SEA | HEAD, SMART DUAL ROLL, SMART-3 ROLLING CODE, COCCINELLA ROLL | |
| SEAV | BE HAPPY RS | |
| SECULUX | NEO | |
| SILVELOX | Mhz 2007, QUARZ SAW | |
| SIMINOR | CVXNL, MITTO | |
| SIMINOR | SIM433 | |
| SOMFY | K-EASY, K-EASY NEW, K-EASY OLD, MITTO, KEY GO RTS, TELIS RTS, KEYTIS RTS, KEYTIS RTS NS, ALARMA | |

COMPATIBILITÀ **FACILE** MULTIFREQUENZA

FACILE MULTIFREQUENCY COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



AGIRE SULLA RICEVENTE
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELLO / MODEL | TIPOLOGIA / MODE |
|---------------|--|------------------|
| SOMMER | 4010, 4011, 4014 TX03-434-2, 4013 TX03-434-4, 4020 TX03-868-4, 4026 TX03-868-2, 4022 TX02-434-2, 4025 TX02-868-2, 4031 TX08-868-4 | |
| STAGNOLI | KALLISTO, VENUS AV223 | |
| TAU | 250K-SLIMRP, 250K-SLIMR, 250T-4RP | |
| TELCOMA | FM400E, FM400 | |
| TORREC | H101 | |
| TOR LIFT | TORMIT4 | |
| V2 | TSC, TXC, TRC, HANDY, PHOENIX, PHOX 433 | |
| VDS | ECO-R, TRQ P | |